

Electrocardiography (ECG) Assembled Sensor Data Sheet

BUNDLE-ECG-UCE6 280920

SPECIFICATIONS

- > Pre-assembled [Electrocardiography \(ECG\)](#) sensor
- > Single cable connection

FEATURES

- > Allows basic ECG data acquisition
- > Easy to wear
- > Plug & play design
- > Raw data acquisition

APPLICATIONS

- > Heart rate & heart rate variability
- > Human-Computer Interaction
- > Biometrics
- > Affective Computing
- > Physiology studies
- > Psychophysiology
- > Biofeedback
- > Biomedical devices prototyping

GENERAL DESCRIPTION

The BITalino assembled ECG sensor is designed for everyone who wants to measure cardiac activity by evaluating ECG signals. This bundle is completely assembled with our 3D Printed Casing for BITalino (r)evolution Plugged making it more convenient to use, wearable, sharable & transportable. The Assembled ECG Sensors with assembled 3-lead electrode cable allow repeatedly accurate & fast measurements.



Fig. 1. Assembled ECG sensor – top view.



Fig. 2. Assembled ECG sensor – from the inside.




Fig. 3. Typical raw ECG data (acquired with BITalino (r)evolution) using an Einthoven triangle configuration.



Fig. 4. Example of an assembled ECG placement with IN+ & IN- on the collarbones and REF on the iliac crest.

bitalino

PLUX – Wireless Biosignals, S.A.
Av. 5 de Outubro, n. 70 – 2
1050-059 Lisbon, Portugal
bitalino@plux.info
<http://bitalino.com/>

REV A

© 2020 PLUX 

This information is provided "as is," and we make no express or implied warranties whatsoever with respect to functionality, operability, use, fitness for a particular purpose, or infringement of rights. We expressly disclaim any liability whatsoever for any direct, indirect, consequential, incidental or special damages, including, without limitation, lost revenues, lost profits, losses resulting from business interruption or loss of data, regardless of the form of action or legal theory under which the liability may be asserted, even if advised of the possibility of such damages.



BEWARE: DIRECT OR INDIRECT COUPLING TO THE MAINS MAY RESULT IN SHOCKING HAZARD



Electrocardiography (ECG) Assembled Sensor Data Sheet

TRANSFER FUNCTION

[ECG datasheet](#)

PHYSICAL CHARACTERISTICS

[ECG datasheet](#)

PACKAGING

Weight: 19 g

ORDERING GUIDE

Part #	Description
BUNDLE-ECG- UCE6	Pre-assembled sensor for cardiac activity measurement.